

Specification of machine

Semi-automatic packaging machine MJL-1C3

Main Feature

- ① It match the national GMP standards and food hygiene certification, all stainless steel machine (it can be customized 316L material)
- ② Imported touch screen, PLC control, industrial Ethernet communications can be connected to the plant DCS control center, stability, anti-interference, easy, intuitive, and long lifetime.
- 3 Auger feeder, with the advantage of high accuracy, speed, etc
- 4 Adjust the operating parameters of product formulations can be stored, for later use, it Manye Packaging—Specialize in power and particle pack and researching control technology for conveyor

can store maximum 10 sets of operating parameters

- ⑤Using the new packing scale weighing system, high-precision and high-speed measurement, with overshoot suppression, drop correction, tolerance alarm function
- ⑥ Devices using the new folder bag, sealing, size can be replaced, it is able to adapt a variety of sizes bags.

The application

The equipment is suitable for packaging powder and granular materials such as flour, milk powder, feed, rice flour, cocoa powder, solid drink, sugar, cotton, sugar, monosodium glutamate, veterinary medicine, glucose, solid medicine, powder additives, carbon powder, talcum powder, pesticide, dye, flavor spices such as measuring and weighing feedback work.

Technical parameters

Model	MJL-1C3	Power Supply	380/220v 50-60Hz	
Packaging weight	1-30kg	Power	2.25kw	
Packaging	<±0.2%	Total Weight	350kg	
Accuracy		Total Weight	330Kg	
Packaging	3bag/min	Total size	1180(L)X1230(W)X2680(H)mm	
Speed			1100(2)/11200(11)/11111	

Device List

MJL-1C3 High does packaging machine

NO.	Name	Brand	Place	Remark
1	Touch screen	Siemens	Germany	
2	PLC	Siemens	Germany	
3	Weight control	Toledo	Switzerland	
4	Breaker	Schneider	France	
5	Relay	Schneider	France	
6	Co contactor	Schneider	France	
7	Thermal relay	Schneider	France	
8	Amphenol connector	Tiande	Tai wan	
9	Emergency Stop	Siemens	Germany	
	Switch			
10	Option switch	Siemens	Germany	
11	The steam cylinder	Air TAC	Tai wan	
12	Solenoid valve	Air TAC	Tai wan	
13	Proximity switch	AUTONISIC	Korean	