











D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-01E-0/AIM 5021











Container Size	20V				
Name/Illustration	ϕ 28.75mm				
1. Starwheel [A0] 	20V-A0 Light brown (1)				
2. Starwheel [A] 	20V-A Light brown (1)				
3. Starwheel [C] 	20V-C Light brown (1)				
4. Starwheel [D] 	20V-D Light brown (1)				
5. Starwheel [E] 	20V-E Light brown (1)				
6. Starwheel [F] 	20V-F Light brown (1)				
7. Starwheel [G] 	20V-G Light brown (1)				
8. Guide [A0-1] 	20V-A0-1 Light brown (1)				
9. Guide [A0-2] 	20V-A0-2 Light brown (1)				
10. Guide [A0-3] 	20V-A0-3 Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-02E-0/AIM 5021











Container Size	20V				
Name/Illustration	ϕ 28.75mm				
11. Guide [A0-4] 	20V-A0-4 Light brown (1)				
12. Guide [A0-5] 	20V-A0-5 Light brown (1)				
13. Guide [A0-6] 	20V-A0-6 Light brown (1)				
14. Guide [A0-7] 	20V-A0-7 Light brown (1)				
15. Guide [A0-8] 	20V-A0-8 Light brown (1)				
16. Guide [A0-9] 	20V-A0-9 Light brown (1)				
17. Guide [A0-10] 	20V-A0-10 Light brown (1)				
18. Guide [A0-11] 	20V-A0-11 Light brown (1)				
19. Guide [A0-12] 	20V-A0-12 Light brown (1)				
20. Infeed screw 	20V Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-03E-0/AIM 5021











Container Size	20V				
Name/Illustration	ϕ 28.75mm				
21. Guide [A1] 	20V-A1 Light brown (1)				
22. Guide [A2] 	20V-A2 Light brown (1)				
23. Guide [A3] 	20V-A3 Light brown (1)				
24. Guide [C] 	20V-C Light brown (1)				
25. Guide [D1] 	20V-D1 Light brown (1)				
26. Guide [D2] 	20V-D2 Light brown (1)				
27. Guide [E1] 	20V-E1 Light brown (1)				
28. Guide [E2] 	20V-E2 Light brown (1)				
29. Guide [F1] 	20V-F1 Light brown (1)				
30. Guide [F2] 	20V-F2 Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-04E-0/AIM 5021











Container Size Name/Illustration	20V				
	ϕ 28.75mm				
31. Guide [G1] 	20V-G1 Light brown (1)				
32. Guide [G2] 	20V-G2 Light brown (1)				
33. Guide [G3] 	20V-G3 Light brown (1)				
34. Guide [G4] 	20V-G4 Light brown (1)				
35. Guide [G5] 	20V-G5 Light brown (1)				
36. Guide [G6] 	20V-G6 Light brown (1)				
37. Rail [A0-2] 	A0-2 20V Light brown (1)				
38. Rail [A0-3] 	A0-3 20V Light brown (1)				
39. Rail [A-1] 	A-1 20V Light brown (1)				
40. Rail [A-2] 	A-2 20V Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-05E-0/AIM 5021











Container Size	20V				
Name/Illustration	ϕ 28.75mm				
41. Rail [A-3] 	A-3 20V Light brown (1)				
42. Rail [A-4] 	A-4 20V Light brown (1)				
43. Rail [C-1] 	C-1 20V Light brown (1)				
44. Trasfer guide [A] 	20V-A Light brown (1)				
45. Cam spacer (RT[a]) 	20V Light brown (1)				
46. Base attachment (RT[a]) 	Light brown (48)				
 (Blank)	Not applied				
47. Camera spacer (C01) 	20V/C01 Light brown (1)				
48. Camera spacer (C02) Height 	20V/C02 Light brown (1)				
49. Camera spacer (C02) Width 	20V/C02 Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-06E-0/AIM 5021











Container Size	20V				
Name/Illustration	ϕ 28.75mm				
50. Camera spacer (C03) Height 	20V/C03 Light brown (1)				
51. Camera spacer (C03) Width 	20V/C03 Light brown (1)				
52. Camera spacer (S) (C1) Width 	20V/C1 Light brown (1)				
53. Camera spacer (L) (C1) Width 	Not applied				
54. Camera spacer (L) (C1) Height 	Not applied				
55. Turntable guide 	20V Light brown (1)				
56. Turntable guide spacer 	[I]20V Light brown (1)				
57. Stopper plate (Infeed turntable part) 	[I]20V Light brown (1)				
58. Infeed stopper spacer(1) 	20V Light brown (1)				
59. Infeed stopper spacer(2) 	20V Light brown (1)				

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Sep. 06 2020

D962-KSC-07E-0/AIM 5021

Container Size Name/Illustration	20V				
	ϕ 28.75mm				
60. Outfeed conveyor guide spacer 	[O]20V Light brown (4)				
61. Outfeed turntable guide spacer 	[O]20V Light brown (1)				
62. Stopper plate (Outfeed turntable part) 	[O]20V Light brown (1)				
63. Linking conveyor guide spacer 	[L]20V Light brown (4)				
64. Spin spacer (C02) 	C02 20V Light brown (1)				
65. Spin pulley (C02) 	20V Light brown (4)				
66. Spin belt (C02) 	FAB-5ER 17 8x935E (1)				
67. Spin spacer (C03) 	C03 20V Light brown (1)				
68. Spin pulley (C03) 	20V Light brown (3)				
69. Spin belt (C03) 	FAB-5ER 17 8x885E (1)				










 The number in parentheses is the quantity of the item.

D962

SIZE CHANGE PARTS LIST

Sep. 06 2020











D962-KSC-08E-0/AIM 5021

Container Size	20V				
Name/Illustration	ϕ 28.75mm				
70. Safety cover [D2] 	D2 20V Light brown (1)				
71. Safety cover [E2] 	E2 20V Light brown (1)				
72. Safety cover [F2] 	F2 20V Light brown (1)				
73. Safety cover [G2] 	G2 20V Light brown (1)				
74. Cap portion (RT[a])  Small Large	Large (48)				
75. Spindle position (RT[a]) 	②				
76. Sample test guide [A0-13] 	20V-A0-13 Light brown (1)				
77. Sample test guide [A0-14] 	20V-A0-14 Light brown (1)				
78. Sample test guide [A4] 	20V-A4 Light brown (1)				

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-01E-0/AIM 5021











Container Size	2R	10R	50H		
Name/Illustration	φ 16mm	φ 24mm	φ 42.5mm		
1. Starwheel [A0] 	2·4R-A0 Red/Pink (1)	10·15R-A0 White/Green (1)	50H-A0 Yellow (1)		
2. Starwheel [A] 	2·4R-A Red/Pink (1)	10·15R-A White/Green (1)	50H-A Yellow (1)		
3. Starwheel [C] 	2·4R-C Red/Pink (1)	10·15R-C White/Green (1)	50H-C Yellow (1)		
4. Starwheel [D] 	2·4R-D Red/Pink (1)	10·15R-D White/Green (1)	50H-D Yellow (1)		
5. Starwheel [E] 	2·4R-E Red/Pink (1)	10·15R-E White/Green (1)	50H-E Yellow (1)		
6. Starwheel [F] 	2·4R-F Red/Pink (1)	10·15R-F White/Green (1)	50H-F Yellow (1)		
7. Starwheel [G] 	2·4R-G Red/Pink (1)	10·15R-G White/Green (1)	50H-G Yellow (1)		
8. Guide [A0-1] 	2·4R-A0-1 Red/Pink (1)	10·15R-A0-1 White/Green (1)	50H-A0-1 Yellow (1)		
9. Guide [A0-2] 	2·4R-A0-2 Red/Pink (1)	10·15R-A0-2 White/Green (1)	50H-A0-2 Yellow (1)		
10. Guide [A0-3] 	2·4R-A0-3 Red/Pink (1)	10·15R-A0-3 White/Green (1)	50H-A0-3 Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-02E-0/AIM 5021











Container Size	2R	10R	50H		
Name/Illustration	φ 16mm	φ 24mm	φ 42.5mm		
11. Guide [A0-4] 	2·4R-A0-4 Red/Pink (1)	10·15R-A0-4 White/Green (1)	50H-A0-4 Yellow (1)		
12. Guide [A0-5] 	2·4R-A0-5 Red/Pink (1)	10·15R-A0-5 White/Green (1)	50H-A0-5 Yellow (1)		
13. Guide [A0-6] 	2·4R-A0-6 Red/Pink (1)	10·15R-A0-6 White/Green (1)	50H-A0-6 Yellow (1)		
14. Guide [A0-7] 	2·4R-A0-7 Red/Pink (1)	10·15R-A0-7 White/Green (1)	50H-A0-7 Yellow (1)		
15. Guide [A0-8] 	2·4R-A0-8 Red/Pink (1)	10·15R-A0-8 White/Green (1)	50H-A0-8 Yellow (1)		
16. Guide [A0-9] 	2·4R-A0-9 Red/Pink (1)	10·15R-A0-9 White/Green (1)	50H-A0-9 Yellow (1)		
17. Guide [A0-10] 	2·4R-A0-10 Red/Pink/Pink (1)	10·15R-A0-10 White/Green (1)	50H-A0-10 Yellow (1)		
18. Guide [A0-11] 	2·4R-A0-11 Red/Pink (1)	10·15R-A0-11 White/Green (1)	50H-A0-11 Yellow (1)		
19. Guide [A0-12] 	2·4R-A0-12 Red/Pink (1)	10·15R-A0-12 White/Green (1)	50H-A0-12 Yellow (1)		
20. Infeed screw 	2R/4R Red/Pink (1)	10R/15R White/Green (1)	42.5 Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-03E-0/AIM 5021











Container Size	2R	10R	50H		
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 42.5mm		
21. Guide [A1] 	2·4R-A1 Red/Pink (1)	10·15R-A1 White/Green (1)	50H-A1 Yellow (1)		
22. Guide [A2] 	2·4R-A2 Red/Pink (1)	10·15R-A2 White/Green (1)	50H-A2 Yellow (1)		
23. Guide [A3] 	2·4R-A3 Red/Pink (1)	10·15R-A3 White/Green (1)	50H-A3 Yellow (1)		
24. Guide [C] 	2·4R-C Red/Pink (1)	10·15R-C White/Green (1)	50H-C Yellow (1)		
25. Guide [D1] 	2·4R-D1 Red/Pink (1)	10·15R-D1 White/Green (1)	50H-D1 Yellow (1)		
26. Guide [D2] 	2·4R-D2 Red/Pink (1)	10·15R-D2 White/Green (1)	50H-D2 Yellow (1)		
27. Guide [E1] 	2·4R-E1 Red/Pink (1)	10·15R-E1 White/Green (1)	50H-E1 Yellow (1)		
28. Guide [E2] 	2·4R-E2 Red/Pink (1)	10·15R-E2 White/Green (1)	50H-E2 Yellow (1)		
29. Guide [F1] 	2·4R-F1 Red/Pink (1)	10·15R-F1 White/Green (1)	50H-F1 Yellow (1)		
30. Guide [F2] 	2·4R-F2 Red/Pink (1)	10·15R-F2 White/Green (1)	50H-F2 Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-04E-0/AIM 5021











Container Size	2R	10R	50H		
Name/Illustration	φ 16mm	φ 24mm	φ 42.5mm		
31. Guide [G1] 	2·4R-G1 Red/Pink (1)	10·15R-G1 White/Green (1)	50H-G1 Yellow (1)		
32. Guide [G2] 	2·4R-G2 Red/Pink (1)	10·15R-G2 White/Green (1)	50H-G2 Yellow (1)		
33. Guide [G3] 	2·4R-G3 Red/Pink (1)	10·15R-G3 White/Green (1)	50H-G3 Yellow (1)		
34. Guide [G4] 	2·4R-G4 Red/Pink (1)	10·15R-G4 White/Green (1)	50H-G4 Yellow (1)		
35. Guide [G5] 	2·4R-G5 Red/Pink (1)	10·15R-G5 White/Green (1)	50H-G5 Yellow (1)		
36. Guide [G6] 	2·4R-G6 Red/Pink (1)	10·15R-G6 White/Green (1)	50H-G6 Yellow (1)		
37. Rail [A0-2] 	A0-2 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)	A0-2 20R/Orange 30R/Blue 50H/Yellow (1)	
38. Rail [A0-3] 	A0-3 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)	A0-3 20R/Orange 30R/Blue 50H/Yellow (1)	
39. Rail [A-1] 	A-1 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)	A-1 20R/Orange 30R/Blue 50H/Yellow (1)	
40. Rail [A-2] 	A-2 2R/Red 4R/Pink (1)	A-2 10R/White 15R/Green (1)	A-2 50H/Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Dec. 19 2019

D962-KSC-05E-1/AIM 5021











Container Size	2R	10R	50H		
Name/Illustration	φ 16mm	φ 24mm	φ 42.5mm		
41. Rail [A-3] 	A-3 2R/Red 4R/Pink (1)	A-3 10R/White 15R/Green (1)	A-3 50H/Yellow (1)		
42. Rail [A-4] 	A-4 2R/Red 4R/Pink (1)	A-4 10R/White 15R/Green (1)	A-4 50H/Yellow (1)		
43. Rail [C-1] 	C-1 2R/Red 4R/Pink (1)	C-1 10R/White 15R/Green (1)	C-1 50H/Yellow (1)		
44. Trasfer guide [A] 	2·4R-A Red/Pink (1)	10·15R-A White/Green (1)	50H-A Yellow (1)		
45. Cam spacer (RT[a]) 	2R Red (1)	10R White (1)	50H Yellow (1)		
46. Base attachment (RT[a]) 	Red/Pink (48)	White/Green (48)	Yellow (Odd:24)		
 (Blank)	Not applied	Not applied	Orange Blue Yellow (Even:24)		
47. Camera spacer (C01) 	TBD		50H/C01 Yellow (1)		
48. Camera spacer (C02) Height 	TBD		50H/C02 Yellow (1)		
49. Camera spacer (C02) Width 	TBD		50H/C02 Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-06E-0/AIM 5021











Container Size Name/Illustration	2R	10R	50H		
	ϕ 16mm	ϕ 24mm	ϕ 42.5mm		
50. Camera spacer (C03) Height 	TBD		50H/C03 Yellow (1)		
51. Camera spacer (C03) Width 	TBD		50H/C03 Yellow (1)		
52. Camera spacer (S) (C1) Width 	TBD		Not applied		
53. Camera spacer (L) (C1) Width 	TBD		50H/C1 Yellow (1)		
54. Camera spacer (L) (C1) Height 	TBD		50H/C1 Yellow (1)		
55. Turntable guide 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	50H Yellow (1)		
56. Turntable guide spacer 	[I]2R/Red [I]4R/Pink (1)	[I]10R/White [I]15R/Green (1)	[I]50H Yellow (1)		
57. Stopper plate (Infeed turntable part) 	[I]2·4R Red/Pink (1)	[I]10·15R White/Green (1)	[I]50H Yellow (1)		
58. Infeed stopper spacer(1) 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	50H Yellow (1)		
59. Infeed stopper spacer(2) 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	50H Yellow (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Dec. 19 2019

D962-KSC-07E-1/AIM 5021










Container Size Name/Illustration	2R	10R	50H		
	φ 16mm	φ 24mm	φ 42.5mm		
60. Outfeed conveyor guide spacer 	[O] 2R/Red [O] 4R/Pink (4)	[O] 10R/White [O] 15R/Green (4)	[O] 50H Yellow (4)		
61. Outfeed turntable guide spacer 	[O] 2R/Red [O] 4R/Pink (1)	[O] 10R/White [O] 15R/Green (1)	[O] 50H Yellow (1)		
62. Stopper plate (Outfeed turntable part) 	[O] 2·4R Red/Pink (1)	[O] 10R·15R White/Green (1)	[O] 50H Yellow (1)		
63. Linking conveyor guide spacer 	[L] 2R/Red [L] 4R/Pink (4)	[L] 10R/White [L] 15R/Green (4)	[L] 50H Yellow (4)		
64. Spin spacer (C02) 	C02 2R/Red 4R/Pink (1)	C02 10R/White 15R/Green (1)	50H/C02 Yellow (1)		
65. Spin pulley (C02) 	2R/Red 4R/Pink (4)	10R/White 15R/Green (4)	20R/Orange 30R/Blue 50H/Yellow (4)		
66. Spin belt (C02) 	FAB-5ER 10 8x935E (1)	FAB-5ER 10 17x935E (1)	FAB-5ER 10 20x935E (1)		
67. Spin spacer (C03) 	C03 2R/Red 4R/Pink (1)	C03 10R/White 15R/Green (1)	50H/C03 Yellow (1)		
68. Spin pulley (C03) 	2R/Red 4R/Pink (3)	10R/White 15R/Green (3)	20R/Orange 30R/Blue 50H/Yellow (3)		
69. Spin belt (C03) 	FAB-5ER 10 8x885E (1)	FAB-5ER 10 17x885E (1)	FAB-5ER 10 20x885E (1)		

 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

Nov. 18 2019

D962-KSC-08E-0/AIM 5021

Container Size	2R	10R	50H		
Name/Illustration	φ 16mm	φ 24mm	φ 42.5mm		
70. Safety cover [D2] 	D2 2R/Red (1)	D2 10R/White (1)	D2 50H/Yellow (1)		
71. Safety cover [E2] 	E2 2R/Red (1)	E2 10R/White (1)	E2 50H/Yellow (1)		
72. Safety cover [F2] 	F2 2R/Red (1)	F2 10R/White (1)	F2 50H/Yellow (1)		
73. Safety cover [G2] 	G2 2R/Red (1)	G2 10R/White (1)	G2 50H/Yellow (1)		
74. Cap portion (RT[a]) 	Small (48)	Large (48)	Large (24)		
75. Spindle position (RT[a]) 		①	③		
76. Sample test guide [A0-13] 	2·4R-A0-13 Red/Pink (1)	10·15R-A0-13 White/Green (1)	50H-A0-13 Yellow (1)		
77. Sample test guide [A0-14] 	2·4R-A0-14 Red/Pink (1)	10·15R-A0-14 White/Green (1)	50H-A0-14 Yellow (1)		
78. Sample test guide [A4] 	2·4R-A4 Red/Pink (1)	10·15R-A4 White/Green (1)	50H-A4 Yellow (1)		

 The number in parentheses is the quantity of the item.











D962

SIZE CHANGE PARTS LIST

Jan.30,2020

4R / 15R / 20R / 30R

D962-KSC-09E-0/AIM 5021

Container Size	4R	15R	20R	30R	
Name/Illustration	φ 16mm	φ 24mm	φ 30mm	φ 30mm	
1. Starwheel [A0] 	2·4R-A0 Red/Pink (1)	10·15R-A0 White/Green (1)	20·30R-A0 Orange/Blue (1)		
2. Starwheel [A] 	2·4R-A Red/Pink (1)	10·15R-A White/Green (1)	20·30R-A Orange/Blue (1)		
3. Starwheel [C] 	2·4R-C Red/Pink (1)	10·15R-C White/Green (1)	20·30R-C Orange/Blue (1)		
4. Starwheel [D] 	2·4R-D Red/Pink (1)	10·15R-D White/Green (1)	20·30R-D Orange/Blue (1)		
5. Starwheel [E] 	2·4R-E Red/Pink (1)	10·15R-E White/Green (1)	20·30R-E Orange/Blue (1)		
6. Starwheel [F] 	2·4R-F Red/Pink (1)	10·15R-F White/Green (1)	20·30R-F Orange/Blue (1)		
7. Starwheel [G] 	2·4R-G Red/Pink (1)	10·15R-G White/Green (1)	20·30R-G Orange/Blue (1)		
8. Guide [A0-1] 	2·4R-A0-1 Red/Pink (1)	10·15R-A0-1 White/Green (1)	20·30R-A0-1 Orange/Blue (1)		
9. Guide [A0-2] 	2·4R-A0-2 Red/Pink (1)	10·15R-A0-2 White/Green (1)	20·30R-A0-2 Orange/Blue (1)		
10. Guide [A0-3] 	2·4R-A0-3 Red/Pink (1)	10·15R-A0-3 White/Green (1)	20·30R-A0-3 Orange/Blue (1)		











 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

Jan.30,2020

D962-KSC-10E-0/AIM 5021

Container Size	4R	15R	20R	30R	
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
11. Guide [A0-4] 	2·4R-A0-4 Red/Pink (1)	10·15R-A0-4 White/Green (1)	20·30R-A0-4 Orange/Blue (1)		
12. Guide [A0-5] 	2·4R-A0-5 Red/Pink (1)	10·15R-A0-5 White/Green (1)	20·30R-A0-5 Orange/Blue (1)		
13. Guide [A0-6] 	2·4R-A0-6 Red/Pink (1)	10·15R-A0-6 White/Green (1)	20·30R-A0-6 Orange/Blue (1)		
14. Guide [A0-7] 	2·4R-A0-7 Red/Pink (1)	10·15R-A0-7 White/Green (1)	20·30R-A0-7 Orange/Blue (1)		
15. Guide [A0-8] 	2·4R-A0-8 Red/Pink (1)	10·15R-A0-8 White/Green (1)	20·30R-A0-8 Orange/Blue (1)		
16. Guide [A0-9] 	2·4R-A0-9 Red/Pink (1)	10·15R-A0-9 White/Green (1)	20·30R-A0-9 Orange/Blue (1)		
17. Guide [A0-10] 	2·4R-A0-10 Red/Pink (1)	10·15R-A0-10 White/Green (1)	20·30R-A0-10 Orange/Blue (1)		
18. Guide [A0-11] 	2·4R-A0-11 Red/Pink (1)	10·15R-A0-11 White/Green (1)	20·30R-A0-11 Orange/Blue (1)		
19. Guide [A0-12] 	2·4R-A0-12 Red/Pink (1)	10·15R-A0-12 White/Green (1)	20·30R-A0-12 Orange/Blue (1)		
20. Infeed screw 	2R/4R Red/Pink (1)	10R/15R White/Green (1)	20R/30R Orange/Blue (1)		

⚠ The number in parentheses is the quantity of the item.











D962

SIZE CHANGE PARTS LIST

Jan.30,2020

4R / 15R / 20R / 30R

D962-KSC-11E-0/AIM 5021

Container Size Name/Illustration	4R	15R	20R	30R	
	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
21. Guide [A1] 	2·4R-A1 Red/Pink (1)	10·15R-A1 White/Green (1)	20·30R-A1 Orange/Blue (1)		
22. Guide [A2] 	2·4R-A2 Red/Pink (1)	10·15R-A2 White/Green (1)	20·30R-A2 Orange/Blue (1)		
23. Guide [A3] 	2·4R-A3 Red/Pink (1)	10·15R-A3 White/Green (1)	20·30R-A3 Orange/Blue (1)		
24. Guide [C] 	2·4R-C Red/Pink (1)	10·15R-C White/Green (1)	20·30R-C Orange/Blue (1)		
25. Guide [D1] 	2·4R-D1 Red/Pink (1)	10·15R-D1 White/Green (1)	20·30R-D1 Orange/Blue (1)		
26. Guide [D2] 	2·4R-D2 Red/Pink (1)	10·15R-D2 White/Green (1)	20·30R-D2 Orange/Blue (1)		
27. Guide [E1] 	2·4R-E1 Red/Pink (1)	10·15R-E1 White/Green (1)	20·30R-E1 Orange/Blue (1)		
28. Guide [E2] 	2·4R-E2 Red/Pink (1)	10·15R-E2 White/Green (1)	20·30R-E2 Orange/Blue (1)		
29. Guide [F1] 	2·4R-F1 Red/Pink (1)	10·15R-F1 White/Green (1)	20·30R-F1 Orange/Blue (1)		
30. Guide [F2] 	2·4R-F2 Red/Pink (1)	10·15R-F2 White/Green (1)	20·30R-F2 Orange/Blue (1)		











 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

Jan.30,2020

D962-KSC-12E-0/AIM 5021











Container Size	4R	15R	20R	30R	
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
31. Guide [G1] 	2·4R-G1 Red/Pink (1)	10·15R-G1 White/Green (1)	20·30R-G1 Orange/Blue (1)		
32. Guide [G2] 	2·4R-G2 Red/Pink (1)	10·15R-G2 White/Green (1)	20·30R-G2 Orange/Blue (1)		
33. Guide [G3] 	2·4R-G3 Red/Pink (1)	10·15R-G3 White/Green (1)	20·30R-G3 Orange/Blue (1)		
34. Guide [G4] 	2·4R-G4 Red/Pink (1)	10·15R-G4 White/Green (1)	20·30R-G4 Orange/Blue (1)		
35. Guide [G5] 	2·4R-G5 Red/Pink (1)	10·15R-G5 White/Green (1)	20·30R-G5 Orange/Blue (1)		
36. Guide [G6] 	2·4R-G6 Red/Pink (1)	10·15R-G6 White/Green (1)	20·30R-G6 Orange/Blue (1)		
37. Rail [A0-2] 	A0-2 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)		A0-2 20R/Orange 30R/Blue 50H/Yellow (1)
38. Rail [A0-3] 	A0-3 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)		A0-3 20R/Orange 30R/Blue 50H/Yellow (1)
39. Rail [A-1] 	A-1 2R/Red 4R/Pink (1)		10R/White 15R/Green (1)		A-1 20R/Orange 30R/Blue 50H/Yellow (1)
40. Rail [A-2] 	A-2 2R/Red 4R/Pink (1)	A-2 10R/White 15R/Green (1)	A-2 20R/Orange 30R/Blue (1)		

⚠ The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

D962-KSC-13E-0/AIM 5021











Container Size	4R	15R	20R	30R	
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
41. Rail [A-3] 	A-3 2R/Red 4R/Pink (1)	A-3 10R/White 15R/Green (1)	A-3 20R/Orange 30R/Blue (1)		
42. Rail [A-4] 	A-4 2R/Red 4R/Pink (1)	A-4 10R/White 15R/Green (1)	A-4 20R/Orange 30R/Blue (1)		
43. Rail [C-1] 	C-1 2R/Red 4R/Pink (1)	C-1 10R/White 15R/Green (1)	C-1 20R/Orange 30R/Blue (1)		
44. Trasfer guide [A] 	2·4R-A Red/Pink (1)	10·15R-A White/Green (1)	20·30R-A Orange/Blue (1)		
45. Cam spacer (RT[a]) 	4R Pink (1)	15R Green (1)	20R Orange (1)	30R Blue (1)	
46. Base attachment (RT[a]) 	Red/Pink (48)	White/Green (48)	Orange/Blue (Odd:24)		
	 (Blank)	Not applied	Not applied	Orange Blue Yellow (Even:24)	
47. Camera spacer (C01) 	TBD				
48. Camera spacer (C02) Height 	TBD				
49. Camera spacer (C02) Width 	TBD				

D962

SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

D962-KSC-14E-0/AIM 5021

Container Size	4R	15R	20R	30R	
Name/Illustration	φ 16mm	φ 24mm	φ 30mm	φ 30mm	
50. Camera spacer (C03) Height 	TBD				
51. Camera spacer (C03) Width 	TBD				
52. Camera spacer (S) (C1) Width 	TBD				
53. Camera spacer (L) (C1) Width 	TBD				
54. Camera spacer (L) (C1) Height 	TBD				
55. Turntable guide 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	20R/Orange 30R/Blue (1)		
56. Turntable guide spacer 	[I]2R/Red [I]4R/Pink (1)	[I]10R/White [I]15R/Green (1)	[I]20R/Orange [I]30R/Blue (1)		
57. Stopper plate (Infeed turntable part) 	[I]2·4R Red/Pink (1)	[I]10·15R White/Green (1)	[I]20·30R Orange/Blue (1)		
58. Infeed stopper spacer(1) 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	20R/Orange 30R/Blue (1)		
59. Infeed stopper spacer(2) 	2R/Red 4R/Pink (1)	10R/White 15R/Green (1)	20R/Orange 30R/Blue (1)		











 The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

Jan.30,2020

D962-KSC-15E-0/AIM 5021











Container Size	4R	15R	20R	30R	
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
60. Outfeed conveyor guide spacer 	[O] 2R/Red [O] 4R/Pink (4)	[O] 10R/White [O] 15R/Green (4)	[O] 20R/Orange [O] 30R/Blue (4)		
61. Outfeed turntable guide spacer 	[O] 2R/Red [O] 4R/Pink (1)	[O] 10R/White [O] 15R/Green (1)	[O] 20R/Orange [O] 30R/Blue (1)		
62. Stopper plate (Outfeed turntable part) 	[O] 2·4R Red/Pink (1)	[O] 10R·15R White/Green (1)	[O] 20R·30R Orange/Blue (1)		
63. Linking conveyor guide spacer 	[L] 2R/Red [L] 4R/Pink (4)	[L] 10R/White [L] 15R/Green (4)	[L] 20R/Orange [L] 30R/Blue (4)		
64. Spin spacer (C02) 	C02 2R/Red 4R/Pink (1)	C02 10R/White 15R/Green (1)	C02 20R/Orange 30R/Blue (1)		
65. Spin pulley (C02) 	2R/Red 4R/Pink (4)	10R/White 15R/Green (4)	20R/Orange 30R/Blue 50H/Yellow (4)		
66. Spin belt (C02) 	FAB-5ER 10 8x935E (1)	FAB-5ER 10 17x935E (1)	FAB-5ER 10 20x935E (1)		
67. Spin spacer (C03) 	C03 2R/Red 4R/Pink (1)	C03 10R/White 15R/Green (1)	C03 20R/Orange 30R/Blue (1)		
68. Spin pulley (C03) 	2R/Red 4R/Pink (3)	10R/White 15R/Green (3)	20R/Orange 30R/Blue 50H/Yellow (3)		
69. Spin belt (C03) 	FAB-5ER 10 8x885E (1)	FAB-5ER 10 17x885E (1)	FAB-5ER 10 20x885E (1)		

⚠ The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

4R / 15R / 20R / 30R

D962-KSC-16E-0/AIM 5021

Container Size	4R	15R	20R	30R	
Name/Illustration	ϕ 16mm	ϕ 24mm	ϕ 30mm	ϕ 30mm	
70. Safety cover [D2] 	D2 4R/Pink (1)	D2 15R/Green (1)	D2 20R/Orange (1)	D2 30R/Blue (1)	
71. Safety cover [E2] 	E2 4R/Pink (1)	E2 15R/Green (1)	E2 20R/Orange (1)	E2 30R/Blue (1)	
72. Safety cover [F2] 	F2 4R/Pink (1)	F2 15R/Green (1)	F2 20R/Orange (1)	F2 30R/Blue (1)	
73. Safety cover [G2] 	G2 4R/Pink (1)	G2 15R/Green (1)	G2 20R/Orange (1)	G2 30R/Blue (1)	
74. Cap portion (RT[a])  Small Large	Small (48)	Large (48)	Large (24)		
75. Spindle position (RT[a]) 	①	②		③	
76. Sample test guide [A0-13] 	2·4R-A0-13 Red/Pink (1)	10·15R-A0-13 White/Green (1)	20·30R-A0-13 Orange/Blue (1)		
77. Sample test guide [A0-14] 	2·4R-A0-14 Red/Pink (1)	10·15R-A0-14 White/Green (1)	20·30R-A0-14 Orange/Blue (1)		
78. Sample test guide [A4] 	2·4R-A4 Red/Pink (1)	10·15R-A4 White/Green (1)	20·30R-A4 Orange/Blue (1)		
79. APC Sensor spacer 	4R Pink (6)	15R Green (6)	30R Blue (6)		





⚠ The number in parentheses is the quantity of the item.

D962 SIZE CHANGE PARTS LIST

50V / 100V / 100H

Mar.23,2020

D962-KSC-17E-0/AIM 5021

Container Size	50V	100V	100H		
Name/Illustration	φ 46mm	φ 49mm	φ 51.6mm		
35. Guide [G5] 	50V-G5 Light green (1)	100V-G5 Purple (1)	100H-G5 Light blue (1)		
36. Guide [G6] 	50V-G6 Light green (1)	100V-G6 Purple (1)	100H-G6 Light blue (1)		
60. Outfeed turntable guide spacer 	[O] 50V Light green (1)	[O] 100V Purple (1)	[O] 100H Light blue (1)		
61. Stopper plate (Outfeed turntable part) 	[O] 50V Light green (1)	[O] 100V Purple (1)	[O] 100H Light blue (1)		

⚠ The number in parentheses is the quantity of the item.